

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMA-MALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE 2 RETURN LOSS (dB)
100.0	0.05	39.4	39.9
200.0	0.07	38.3	38.4
300.0	0.09	41.6	42.0
500.0	0.13	43.5	43.7
600.0	0.14	39.2	40.9
700.0	0.15	40.2	42.4
800.0	0.16	48.3	45.1
900.0	0.17	48.7	42.5
1000.0	0.18	41.6	40.1
1100.0	0.19	40.1	39.0
1250.0	0.21	52.4	51.1
1500.0	0.23	36.5	38.5
1750.0	0.25	49.9	41.9
2000.0	0.26	34.2	34.2
2001.0	0.26	34.2	34.2
2250.0	0.28	46.3	39.3
2500.0	0.29	35.0	35.0
2750.0	0.31	56.7	41.4
3000.0	0.32	32.4	32.8
3250.0	0.33	46.9	37.7
3500.0	0.35	31.7	31.6
4000.0	0.38	29.4	29.8
4250.0	0.39	47.3	38.4
4500.0	0.41	28.6	29.2
5000.0	0.43	29.9	30.1
5500.0	0.43	29.9	29.5
6000.0	0.46	30.4	30.7
6500.0	0.48	28.8	27.6
7000.0	0.49	35.7	33.4
7500.0	0.51	33.8	33.0
8000.0	0.53	43.1	37.5
8500.0	0.54	33.3	34.2
9000.0	0.55	36.2	37.1
9500.0	0.58	31.5	31.6
10000.0	0.57	31.7	31.0
10500.0	0.59	34.6	32.3
11000.0	0.59	35.6	32.2
11500.0	0.61	35.0	32.3
12000.0	0.61	32.9	32.3
12500.0	0.74	26.8	35.4
13000.0	0.72	37.1	28.6
13500.0	0.79	33.9	32.8
14000.0	0.81	35.6	30.6
14500.0	0.76	39.1	32.7
15000.0	0.77	37.0	26.8
15500.0	0.77	37.7	38.3
16000.0	0.76	40.7	34.0
16500.0	0.81	30.5	27.6
17000.0	0.83	28.9	27.4
17500.0	0.86	26.9	29.1
18000.0	0.88	24.7	24.5