

Adapter 1.35mm-Female to 1.85mm-Male**135FR-185M+****Typical Performance Data (+25°C)**

FREQ.	INSERTION LOSS	1.35mm-FEMALE VSWR	1.85mm-MALE VSWR
(GHz)	(dB)	(:1)	(:1)
0.01	0.02	1.01	1.01
0.2	0.03	1.01	1.01
0.4	0.05	1.02	1.02
0.6	0.06	1.02	1.02
0.8	0.07	1.02	1.02
1.0	0.07	1.02	1.03
3.0	0.11	1.04	1.04
5.0	0.12	1.02	1.02
7.0	0.13	1.04	1.04
9.0	0.15	1.09	1.09
11.0	0.17	1.12	1.11
13.0	0.18	1.11	1.10
15.0	0.18	1.06	1.07
17.0	0.18	1.02	1.03
19.0	0.19	1.04	1.04
21.0	0.21	1.10	1.12
23.0	0.23	1.14	1.16
25.0	0.25	1.15	1.16
27.0	0.26	1.10	1.10
29.0	0.25	1.02	1.02
31.0	0.28	1.13	1.12
33.0	0.33	1.25	1.26
35.0	0.35	1.28	1.30
37.0	0.35	1.23	1.24
39.0	0.32	1.10	1.09
41.0	0.32	1.04	1.04
43.0	0.34	1.08	1.10
45.0	0.35	1.10	1.12
47.0	0.38	1.11	1.14
49.0	0.38	1.06	1.05
51.0	0.39	1.04	1.03
53.0	0.41	1.07	1.09
55.0	0.42	1.14	1.16
57.0	0.45	1.17	1.16
59.0	0.45	1.20	1.16
61.0	0.48	1.19	1.21
63.0	0.48	1.10	1.09
65.0	0.48	1.04	1.05
67.0	0.49	1.08	1.07