

Adapter 1.35mm-Male to 1.85mm-Female**135MR-185F+****Typical Performance Data (+25°C)**

FREQ.	INSERTION LOSS	1.35mm-MALE VSWR	1.85mm-FEMALE VSWR
(GHz)	(dB)	(:1)	(:1)
0.01	0.01	1.01	1.01
0.2	0.03	1.01	1.01
0.4	0.05	1.02	1.02
0.6	0.06	1.02	1.02
0.8	0.07	1.03	1.03
1.0	0.07	1.03	1.03
3.0	0.10	1.03	1.04
5.0	0.12	1.01	1.01
7.0	0.14	1.05	1.05
9.0	0.14	1.10	1.09
11.0	0.15	1.11	1.09
13.0	0.16	1.10	1.06
15.0	0.16	1.06	1.03
17.0	0.17	1.04	1.02
19.0	0.18	1.02	1.01
21.0	0.20	1.02	1.03
23.0	0.21	1.10	1.10
25.0	0.23	1.15	1.17
27.0	0.26	1.20	1.20
29.0	0.24	1.13	1.14
31.0	0.24	1.07	1.07
33.0	0.28	1.21	1.20
35.0	0.34	1.34	1.31
37.0	0.36	1.34	1.31
39.0	0.33	1.21	1.21
41.0	0.30	1.06	1.05
43.0	0.32	1.14	1.11
45.0	0.36	1.24	1.23
47.0	0.39	1.25	1.26
49.0	0.37	1.15	1.18
51.0	0.35	1.05	1.05
53.0	0.37	1.11	1.09
55.0	0.39	1.11	1.10
57.0	0.42	1.14	1.14
59.0	0.48	1.26	1.21
61.0	0.52	1.24	1.22
63.0	0.49	1.16	1.13
65.0	0.47	1.03	1.02
67.0	0.52	1.14	1.12