

Adapter 1.35mm-Male to 1.85mm-Male**135MR-185M+****Typical Performance Data (+25°C)**

FREQ.	INSERTION LOSS	1.35mm-MALE VSWR	1.85mm-MALE VSWR
(GHz)	(dB)	(:1)	(:1)
0.01	0.01	1.01	1.01
0.2	0.03	1.01	1.01
0.4	0.05	1.01	1.02
0.6	0.06	1.02	1.02
0.8	0.07	1.02	1.03
1.0	0.07	1.02	1.03
3.0	0.10	1.03	1.03
5.0	0.12	1.02	1.01
7.0	0.14	1.03	1.03
9.0	0.14	1.08	1.07
11.0	0.15	1.12	1.09
13.0	0.16	1.14	1.10
15.0	0.16	1.10	1.09
17.0	0.16	1.04	1.05
19.0	0.17	1.03	1.03
21.0	0.18	1.09	1.09
23.0	0.20	1.13	1.12
25.0	0.21	1.14	1.13
27.0	0.22	1.10	1.12
29.0	0.23	1.06	1.09
31.0	0.24	1.10	1.08
33.0	0.26	1.21	1.17
35.0	0.30	1.30	1.27
37.0	0.31	1.30	1.26
39.0	0.31	1.23	1.22
41.0	0.28	1.12	1.10
43.0	0.29	1.12	1.09
45.0	0.30	1.19	1.16
47.0	0.32	1.18	1.19
49.0	0.33	1.12	1.16
51.0	0.33	1.05	1.08
53.0	0.34	1.11	1.09
55.0	0.36	1.16	1.12
57.0	0.38	1.21	1.13
59.0	0.39	1.22	1.13
61.0	0.39	1.17	1.11
63.0	0.41	1.12	1.11
65.0	0.43	1.09	1.14
67.0	0.47	1.14	1.18