

Hand-Flex Coaxial Cable, SMA-M/N-M

141-18SMNM+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	N-MALE RETURN LOSS (dB)
100.0	0.06	30.0	30.1
200.0	0.09	36.8	37.9
300.0	0.10	35.7	35.3
400.0	0.12	30.4	31.6
500.0	0.14	36.7	38.1
600.0	0.15	29.2	29.6
700.0	0.17	36.3	37.0
800.0	0.18	33.0	32.1
900.0	0.19	30.8	32.3
1000.0	0.20	37.1	37.0
1200.0	0.22	37.2	38.7
1400.0	0.24	35.9	35.8
1600.0	0.26	31.6	31.8
1800.0	0.27	33.0	33.5
2000.0	0.29	34.7	36.5
2200.0	0.30	34.2	34.2
2400.0	0.32	39.3	37.2
2600.0	0.33	39.3	36.9
2800.0	0.35	33.0	32.1
3000.0	0.36	32.8	30.1
3500.0	0.39	31.5	30.0
4000.0	0.42	29.7	28.1
4500.0	0.45	29.8	27.8
5000.0	0.48	29.8	28.9
5500.0	0.51	31.3	30.4
6000.0	0.53	31.0	30.2
6500.0	0.54	33.4	35.2
7000.0	0.59	32.7	35.6
8000.0	0.63	30.8	39.3
8500.0	0.68	35.0	37.6
9000.0	0.70	39.6	32.2
9500.0	0.73	41.2	26.1
10000.0	0.76	49.9	27.6
10500.0	0.78	33.9	24.1
11000.0	0.79	30.2	23.9
11500.0	0.83	26.6	23.7
12000.0	0.85	26.2	24.8
12500.0	0.90	23.1	23.7
13000.0	0.93	23.2	25.1
13500.0	0.93	25.6	28.8
14000.0	0.97	26.6	30.2
14500.0	0.99	27.6	30.9
15000.0	0.99	27.0	28.8
15500.0	0.97	26.2	25.6
16000.0	0.99	24.8	24.8
16500.0	1.01	24.5	23.7
17000.0	1.06	23.9	24.2
17500.0	1.09	22.8	23.3
18000.0	1.08	24.7	21.4