

Adapter, 1.85 mm-Female Right-Angle to 2.92 mm-Male**185FR-KM+***Typical Performance Data*

FREQ.	INSERTION LOSS	1.85 mm-FEMALE VSWR	2.92 mm-MALE VSWR
(GHz)	(dB)	(:1)	(:1)
0.01	0.00	1.01	1.01
0.05	0.01	1.00	1.00
0.10	0.02	1.01	1.01
1.00	0.07	1.02	1.02
2.00	0.08	1.02	1.02
3.00	0.09	1.03	1.01
4.00	0.11	1.04	1.02
5.00	0.12	1.05	1.04
6.00	0.12	1.05	1.05
7.00	0.13	1.04	1.04
8.00	0.13	1.04	1.04
9.00	0.14	1.05	1.05
10.00	0.14	1.05	1.06
11.00	0.15	1.07	1.07
12.00	0.16	1.08	1.10
13.00	0.16	1.09	1.11
14.00	0.16	1.07	1.10
15.00	0.17	1.07	1.08
16.00	0.17	1.07	1.08
17.00	0.18	1.07	1.09
18.00	0.19	1.06	1.06
19.00	0.19	1.06	1.05
20.00	0.20	1.07	1.09
21.00	0.21	1.08	1.10
22.00	0.21	1.08	1.10
23.00	0.22	1.08	1.09
24.00	0.23	1.06	1.09
25.00	0.23	1.05	1.07
26.00	0.23	1.07	1.07
27.00	0.24	1.08	1.09
28.00	0.25	1.08	1.09
29.00	0.25	1.09	1.08
30.00	0.26	1.11	1.11
31.00	0.28	1.15	1.16
32.00	0.29	1.14	1.16
33.00	0.28	1.14	1.15
34.00	0.29	1.13	1.14
35.00	0.30	1.15	1.16
36.00	0.31	1.17	1.19
37.00	0.33	1.20	1.20
38.00	0.35	1.26	1.24
39.00	0.36	1.27	1.26
40.00	0.39	1.27	1.28