

Adapter 1.85, Right-Angle mm-Male to 2.92 mm-Female**185MR-KF+***Typical Performance Data*

FREQ.	INSERTION LOSS	1.85 mm-MALE VSWR	2.92 mm-FEMALE VSWR
(GHz)	(dB)	(:1)	(:1)
0.01	0.00	1.03	1.01
0.05	0.01	1.00	1.00
0.10	0.01	1.01	1.00
1.00	0.04	1.01	1.03
2.00	0.06	1.01	1.04
3.00	0.06	1.01	1.03
4.00	0.07	1.01	1.01
5.00	0.07	1.01	1.01
6.00	0.08	1.03	1.01
7.00	0.08	1.06	1.03
8.00	0.08	1.10	1.06
9.00	0.09	1.14	1.10
10.00	0.10	1.16	1.12
11.00	0.11	1.16	1.14
12.00	0.12	1.14	1.16
13.00	0.13	1.11	1.18
14.00	0.14	1.11	1.19
15.00	0.14	1.16	1.19
16.00	0.14	1.23	1.17
17.00	0.12	1.28	1.13
18.00	0.12	1.30	1.11
19.00	0.13	1.27	1.13
20.00	0.16	1.21	1.17
21.00	0.18	1.13	1.22
22.00	0.20	1.12	1.27
23.00	0.22	1.19	1.33
24.00	0.25	1.27	1.36
25.00	0.24	1.32	1.33
26.00	0.22	1.30	1.26
27.00	0.19	1.25	1.19
28.00	0.18	1.18	1.15
29.00	0.18	1.13	1.12
30.00	0.19	1.14	1.13
31.00	0.21	1.18	1.19
32.00	0.23	1.20	1.24
33.00	0.24	1.18	1.26
34.00	0.24	1.15	1.21
35.00	0.21	1.14	1.08
36.00	0.21	1.17	1.11
37.00	0.25	1.24	1.25
38.00	0.30	1.28	1.33
39.00	0.29	1.24	1.26
40.00	0.26	1.20	1.17