

Adapter, 1.85 mm-Male Right-Angle to 2.92 mm-Male**185MR-KM+***Typical Performance Data*

FREQ.	INSERTION LOSS	1.85 mm-MALE VSWR	2.92 mm-MALE VSWR
(GHz)	(dB)	(:1)	(:1)
0.01	0.00	1.01	1.00
0.05	0.01	1.01	1.00
0.10	0.01	1.01	1.00
1.00	0.04	1.02	1.02
2.00	0.05	1.02	1.02
3.00	0.06	1.01	1.03
4.00	0.07	1.03	1.03
5.00	0.08	1.04	1.04
6.00	0.08	1.04	1.06
7.00	0.08	1.02	1.08
8.00	0.09	1.05	1.10
9.00	0.09	1.08	1.10
10.00	0.10	1.10	1.09
11.00	0.11	1.08	1.07
12.00	0.11	1.05	1.06
13.00	0.11	1.08	1.02
14.00	0.12	1.13	1.04
15.00	0.14	1.15	1.13
16.00	0.15	1.14	1.22
17.00	0.14	1.10	1.29
18.00	0.15	1.11	1.31
19.00	0.16	1.16	1.27
20.00	0.19	1.20	1.24
21.00	0.22	1.21	1.20
22.00	0.22	1.21	1.13
23.00	0.19	1.23	1.03
24.00	0.22	1.28	1.16
25.00	0.27	1.31	1.32
26.00	0.27	1.30	1.40
27.00	0.23	1.26	1.37
28.00	0.21	1.23	1.30
29.00	0.23	1.23	1.27
30.00	0.28	1.26	1.27
31.00	0.29	1.30	1.21
32.00	0.27	1.33	1.16
33.00	0.28	1.34	1.21
34.00	0.31	1.31	1.29
35.00	0.28	1.20	1.28
36.00	0.23	1.10	1.17
37.00	0.23	1.11	1.07
38.00	0.24	1.15	1.05
39.00	0.22	1.17	1.10
40.00	0.22	1.14	1.12