

Non-Magnetic Flex Cable SMA Male to SMA Male

86N-20CSM

Typical Performance Data

FREQ.	INSERTION LOSS	SMA MALE RETURN LOSS IN	SMA MALE RETURN LOSS OUT
(GHz)	(dB)	(dB)	(dB)
0	0.01	46.07	47.49
1	0.13	45.33	47.43
2	0.18	42.45	42.34
3	0.23	41.19	42.54
4	0.27	39.10	38.42
5	0.31	40.00	38.92
6	0.34	38.85	39.04
7	0.37	36.83	37.91
8	0.40	34.45	35.16
9	0.43	35.41	35.63
10	0.46	27.01	27.14
11	0.48	25.01	25.26
12	0.51	28.73	29.81
13	0.53	32.49	33.72
14	0.56	35.13	34.95
15	0.58	32.15	33.02
16	0.60	26.89	27.73
17	0.63	24.58	25.74
18	0.65	26.26	27.20

