

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
0.50	0.98	9.80
0.63	0.70	11.52
0.75	0.54	12.95
0.88	0.45	14.18
1.00	0.38	15.23
1.10	0.35	15.97
1.30	0.30	17.26
1.40	0.28	17.83
1.50	0.26	18.35
3.00	0.19	22.86
4.00	0.18	24.19
5.00	0.17	24.91
6.00	0.17	25.26
7.00	0.17	25.38
8.00	0.17	25.34
9.00	0.17	25.21
10.00	0.17	25.01
11.00	0.17	24.78
12.00	0.17	24.52
13.00	0.17	24.23
14.00	0.17	23.94
15.00	0.18	23.65
20.00	0.19	22.19
25.00	0.20	20.85
30.00	0.22	19.66
35.00	0.24	18.60
40.00	0.25	17.65
50.00	0.28	16.01
60.00	0.32	14.65
70.00	0.35	13.49
80.00	0.37	12.46
90.00	0.41	11.58
100.00	0.43	10.79
110.00	0.46	10.07
120.00	0.49	9.44
130.00	0.51	8.85
140.00	0.53	8.33
150.00	0.54	7.84
167.00	0.56	7.09
184.00	0.57	6.45
201.00	0.59	5.87