

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
0.10	0.77	8.79
0.30	0.32	17.37
0.50	0.30	20.38
0.70	0.30	21.71
0.90	0.30	22.42
1.00	0.29	22.70
3.00	0.20	25.39
5.00	0.17	26.55
7.00	0.16	27.09
9.00	0.16	27.41
10.00	0.16	27.50
15.00	0.16	27.76
20.00	0.16	27.74
25.00	0.17	27.55
30.00	0.18	27.37
35.00	0.19	27.14
40.00	0.19	26.92
45.00	0.20	26.66
50.00	0.20	26.38
55.00	0.21	26.09
60.00	0.21	25.83
65.00	0.23	25.56
70.00	0.24	25.25
75.00	0.24	24.99
80.00	0.24	24.71
85.00	0.24	24.44
90.00	0.25	24.15
95.00	0.26	23.85
100.00	0.26	23.55
150.00	0.34	20.70
200.00	0.42	18.57
250.00	0.52	16.83
300.00	0.66	15.34
350.00	0.83	14.23
400.00	1.06	13.17
450.00	1.33	12.36
500.00	1.68	11.75