

RF Transformer

ADT1-ED8224/1

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
0.15	2.690	7.81
0.20	2.200	9.01
0.25	1.870	10.04
0.30	1.640	10.95
0.35	1.470	11.75
0.40	1.340	12.47
0.45	1.230	13.11
0.50	1.150	13.70
0.55	1.080	14.23
0.60	1.020	14.71
0.80	0.860	16.33
1.20	0.700	18.58
1.50	0.630	19.80
3.00	0.490	23.46
4.50	0.440	25.41
6.00	0.430	26.57
7.50	0.420	27.32
9.00	0.420	27.78
20.00	0.450	29.02
110.00	0.520	29.59
200.00	0.590	27.40
290.00	0.650	24.43
380.00	0.730	21.25
400.00	0.750	20.64
450.00	0.810	19.02
500.00	0.880	17.52
550.00	0.960	16.08
600.00	1.050	14.78
650.00	1.160	13.54
700.00	1.270	12.49
750.00	1.410	11.46
800.00	1.550	10.57
850.00	1.700	9.75
900.00	1.860	9.01
950.00	2.030	8.37
1000.00	2.200	7.78
1200.00	2.890	6.09

