

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
3.00	2.05	4.70
4.00	1.50	6.52
5.00	1.34	7.78
7.00	1.28	9.07
9.00	1.26	9.67
10.00	1.24	9.88
30.00	1.01	11.28
50.00	0.94	11.60
70.00	0.92	11.69
90.00	0.92	11.69
100.00	0.93	11.67
125.00	0.94	11.56
150.00	0.98	11.39
175.00	1.01	11.19
200.00	1.06	10.97
250.00	1.17	10.48
300.00	1.29	9.93
350.00	1.42	9.42
400.00	1.57	8.91
450.00	1.70	8.43
500.00	1.87	7.98
550.00	2.00	7.55
600.00	2.18	7.16
650.00	2.29	6.80
700.00	2.48	6.49
725.00	2.54	6.33
750.00	2.58	6.18
775.00	2.67	6.04
800.00	2.80	5.92
850.00	2.85	5.67
900.00	3.10	5.44
950.00	3.12	5.23
1000.00	3.39	5.04