

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
0.07	1.18	9.19
0.10	0.87	11.88
0.30	0.62	19.97
0.50	0.59	22.71
1.00	0.52	25.46
25.50	0.34	31.39
50.00	0.39	27.39
60.00	0.42	25.78
80.00	0.47	23.02
100.00	0.48	21.23
110.00	0.48	20.64
128.00	0.50	19.70
146.00	0.55	18.66
164.00	0.59	17.90
182.00	0.63	17.18
200.00	0.66	16.64
210.00	0.66	16.53
222.00	0.68	16.15
234.00	0.71	15.55
246.00	0.73	15.28
258.00	0.75	14.99
270.00	0.77	14.70
282.00	0.78	14.43
294.00	0.78	14.17
306.00	0.79	13.93
318.00	0.81	13.73
330.00	0.85	13.51
340.00	0.86	13.43
356.00	0.93	13.13
372.00	0.99	12.85
388.00	1.05	12.57
404.00	1.12	12.22
420.00	1.12	11.95
436.00	1.10	11.83
452.00	1.08	11.77
468.00	1.07	11.69
484.00	1.07	11.57
500.00	1.10	11.46