

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
0.03	2.77	6.60
0.06	1.35	9.76
0.09	0.85	12.03
0.10	0.76	12.69
0.20	0.46	17.26
0.30	0.39	19.69
0.33	0.37	20.15
0.35	0.36	20.55
0.40	0.35	21.24
0.50	0.32	22.33
0.60	0.30	23.16
0.63	0.30	23.34
0.65	0.29	23.50
0.68	0.29	23.66
0.70	0.28	23.81
0.80	0.27	24.35
0.90	0.26	24.82
1.00	0.25	25.23
3.00	0.17	28.87
5.00	0.14	29.98
10.00	0.13	30.80
30.00	0.14	30.36
50.00	0.15	28.92
100.00	0.17	25.28
125.00	0.18	23.75
150.00	0.20	22.39
175.00	0.22	21.22
200.00	0.23	20.18
225.00	0.24	19.28
250.00	0.26	18.45
270.00	0.28	17.86
275.00	0.28	17.70
280.00	0.29	17.56
290.00	0.30	17.27
300.00	0.30	17.00
400.00	0.39	14.72
500.00	0.48	12.95
750.00	0.81	9.89
1000.00	1.25	7.87
1250.00	1.62	6.46
1500.00	2.24	5.45