

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
0.06	0.55	12.87
0.07	0.47	14.13
0.08	0.43	15.24
0.09	0.40	16.26
0.10	0.38	17.17
0.20	0.38	22.62
10.00	0.25	36.02
20.00	0.27	34.95
30.00	0.29	33.48
40.00	0.31	32.03
50.00	0.32	30.71
70.00	0.35	28.52
90.00	0.38	26.75
110.00	0.40	25.28
130.00	0.44	24.02
150.00	0.46	22.85
170.00	0.48	21.78
190.00	0.50	20.77
210.00	0.56	19.84
230.00	0.61	18.96
250.00	0.63	18.12
254.00	0.63	17.95
258.00	0.63	17.75
262.00	0.63	17.60
266.00	0.64	17.46
270.00	0.64	17.31
274.00	0.65	17.27
278.00	0.66	17.18
282.00	0.67	17.02
286.00	0.68	16.87
290.00	0.70	16.70
301.00	0.76	16.29
312.00	0.81	15.81
323.00	0.86	15.45
334.00	0.88	15.07
345.00	0.88	14.71
356.00	0.88	14.35
367.00	0.90	14.02
378.00	0.95	13.69
389.00	1.03	13.35
400.00	1.13	13.03