

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
1.00	2.28	14.27
1.25	1.63	14.57
1.50	1.22	14.88
1.75	0.93	15.17
2.00	0.74	15.45
3.00	0.37	16.42
5.00	0.26	17.78
7.00	0.28	18.54
9.00	0.29	18.88
20.00	0.27	18.95
30.00	0.25	18.77
40.00	0.25	18.65
50.00	0.25	18.58
60.00	0.24	18.50
70.00	0.24	18.42
80.00	0.24	18.36
90.00	0.26	18.28
100.00	0.26	18.18
200.00	0.28	17.23
300.00	0.29	16.19
400.00	0.34	15.41
500.00	0.41	15.05
600.00	0.43	15.10
700.00	0.48	15.37
800.00	0.51	15.92
900.00	0.52	16.98
1000.00	0.53	18.43
1150.00	0.58	21.61
1300.00	0.63	24.37
1450.00	0.76	21.59
1600.00	0.90	17.71
1750.00	1.14	14.77
1900.00	1.37	12.72
2050.00	1.65	11.00
2200.00	1.81	9.65
2350.00	2.06	8.59
2500.00	2.16	8.04
2650.00	2.31	8.12
2800.00	2.32	9.06
2950.00	2.24	10.85
3100.00	2.11	13.63