

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
1.00	0.62	22.14
5.00	0.35	28.79
9.50	0.30	32.17
14.00	0.29	34.11
18.50	0.29	35.30
23.00	0.29	36.32
27.50	0.29	36.97
32.00	0.29	37.52
36.50	0.29	38.06
41.00	0.30	38.46
45.50	0.30	38.76
50.00	0.31	38.99
55.00	0.30	39.22
84.00	0.33	40.82
113.00	0.34	41.46
142.00	0.35	40.82
171.00	0.37	38.97
200.00	0.38	36.91
220.00	0.38	35.68
240.00	0.40	34.50
260.00	0.40	33.44
334.00	0.43	29.49
408.00	0.46	26.64
482.00	0.48	25.33
556.00	0.50	22.78
630.00	0.50	21.69
704.00	0.53	21.34
778.00	0.56	20.29
852.00	0.60	20.68
926.00	0.61	19.95
1000.00	0.66	21.32
1100.00	0.86	19.92
1200.00	0.78	20.77
1300.00	0.87	18.52
1400.00	0.96	16.16
1500.00	1.13	14.39
1600.00	1.34	11.35
1700.00	1.58	10.39
1800.00	1.84	8.79
1900.00	2.08	7.83
2000.00	2.27	7.23