

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
2.00	2.20	10.78
3.00	1.19	11.89
5.00	0.46	14.28
7.00	0.24	16.46
10.00	0.12	19.60
30.00	0.15	32.91
50.00	0.21	48.06
70.00	0.23	38.44
90.00	0.25	33.31
100.00	0.26	31.71
125.00	0.28	28.52
150.00	0.29	26.19
175.00	0.31	24.40
200.00	0.33	22.93
220.00	0.34	21.83
225.00	0.34	21.57
230.00	0.35	21.33
250.00	0.36	20.44
300.00	0.41	18.46
350.00	0.46	16.78
400.00	0.53	15.26
450.00	0.60	13.96
500.00	0.69	12.79
510.00	0.71	12.57
512.00	0.72	12.53
515.00	0.72	12.46
525.00	0.75	12.24
550.00	0.80	11.70
600.00	0.93	10.73
650.00	1.07	9.85
700.00	1.23	9.03
750.00	1.41	8.29
800.00	1.60	7.62
825.00	1.71	7.31
850.00	1.82	7.00
875.00	1.94	6.71
900.00	2.06	6.44
925.00	2.18	6.18
950.00	2.31	5.94
975.00	2.45	5.71
1000.00	2.59	5.48