

Typical Performance Data

FREQUENCY (MHz)	RETURN LOSS (dB)
10	43.34
50	42.51
100	42.34
200	42.25
300	42.08
400	42.00
500	41.88
600	41.67
700	41.46
800	41.38
900	41.39
1000	41.47
2000	41.26
3000	40.68
4000	40.17
5000	41.02
6000	42.48
7000	45.20
8000	49.81
9000	48.48
10000	43.51
11000	39.34
12000	36.24
13000	34.31
14000	32.48
15000	30.92
16000	29.88
17000	28.88
18000	27.96
19000	27.41
20000	27.17
21000	27.13
22000	27.03
23000	27.31
24000	27.75
25000	28.17
26000	28.60
27000	29.10
28000	29.03
29000	28.16
30000	26.73
31000	25.32
32000	24.02
33000	22.81
34000	21.87
35000	21.13
36000	20.60
37000	20.21
38000	19.96
39000	19.95
40000	20.24
41000	20.86
42000	21.71
43000	22.99
44000	24.66
45000	26.42
46000	28.03
47000	28.19
48000	27.09
49000	24.74
50000	22.93