

Flexible Cable 1.0 mm Female to 1.0 mm Female

AP110-0.5-W1F+

Typical Performance Data

FREQ.	INSERTION LOSS	1.0 mm FEMALE RETURN LOSS	1.0 mm FEMALE RETURN LOSS
(GHz)	(dB)	(dB)	(dB)
0	0.06	48.08	47.79
1	0.23	31.34	31.16
3	0.47	27.09	27.25
7	0.68	40.48	41.13
11	0.82	27.36	27.82
15	0.93	33.35	33.59
19	1.02	31.69	31.10
23	1.11	31.71	31.87
27	1.20	33.02	32.87
31	1.29	33.75	35.37
35	1.40	24.18	23.70
39	1.52	19.58	19.45
43	1.55	34.34	33.90
47	1.64	31.25	33.48
51	1.76	27.73	27.50
55	1.89	20.43	20.53
59	1.98	20.04	19.55
63	2.00	30.88	29.74
67	2.09	28.33	28.20
71	2.19	25.66	26.17
75	2.35	21.10	20.65
79	2.39	22.77	24.65
83	2.61	27.71	26.68
87	2.77	23.85	25.61
91	3.07	24.22	23.89
95	3.17	22.27	22.95
99	3.19	28.32	27.79
103	3.16	26.69	26.11
107	3.14	27.52	26.25
110	3.16	28.08	24.14