

Typical Performance Data

FREQ.	INSERTION LOSS	1.0 mm FEMALE RETURN LOSS	1.0 mm MALE RETURN LOSS
(GHz)	(dB)	(dB)	(dB)
0	0.03	53.52	52.09
1	0.21	31.05	31.17
3	0.45	26.75	26.61
7	0.63	36.93	37.74
11	0.76	26.19	29.48
15	0.89	28.93	27.36
19	0.98	31.32	29.41
23	1.07	29.20	35.25
27	1.14	32.99	33.52
31	1.25	29.00	33.30
35	1.34	25.38	28.79
39	1.44	24.74	28.10
43	1.52	24.02	23.17
47	1.58	35.47	29.72
51	1.70	23.67	27.52
55	1.81	19.43	22.64
59	1.88	20.33	24.77
63	1.93	26.45	28.39
67	2.01	28.30	30.57
71	2.10	25.34	28.62
75	2.17	24.43	25.40
79	2.24	28.36	24.07
83	2.46	24.80	25.41
87	2.62	22.50	26.84
91	2.94	21.11	21.78
95	2.99	26.79	23.04
99	3.05	23.96	22.60
103	3.00	26.04	23.38
107	2.98	25.35	26.15
110	2.95	25.20	27.82