

Flexible Cable 1.0 mm Female to 1.0 mm Female

AP110-1FT-W1F+

Typical Performance Data

FREQ.	INSERTION LOSS	1.0 mm FEMALE RETURN LOSS	1.0 mm FEMALE RETURN LOSS
(GHz)	(dB)	(dB)	(dB)
0	0.08	46.51	44.70
1	0.36	30.57	30.30
3	0.77	40.88	40.75
7	1.15	34.16	34.13
11	1.41	28.66	28.57
15	1.62	35.36	35.20
19	1.81	32.15	32.29
23	1.98	28.70	28.90
27	2.16	31.84	31.74
31	2.32	30.46	30.19
35	2.52	21.62	21.84
39	2.70	19.22	19.24
43	2.83	22.02	21.71
47	2.95	34.43	35.46
51	3.13	25.73	27.57
55	3.31	23.06	24.46
59	3.46	22.75	23.04
63	3.58	23.43	23.52
67	3.69	33.25	32.41
71	3.87	23.16	23.22
75	4.04	22.48	22.75
79	4.13	24.89	27.93
83	4.43	28.78	27.45
87	4.67	22.54	22.92
91	5.07	20.06	19.50
95	5.19	23.44	22.98
99	5.28	29.68	27.45
103	5.30	26.98	28.75
107	5.36	27.56	26.35
110	5.40	24.79	23.12

