

Flexible Cable 1.0 mm Female to 1.0 mm Male

AP110-1FTW1F1M+

Typical Performance Data

FREQ.	INSERTION LOSS	1.0 mm FEMALE RETURN LOSS	1.0 mm MALE RETURN LOSS
(GHz)	(dB)	(dB)	(dB)
0	0.05	48.26	46.79
1	0.35	30.77	31.12
3	0.74	45.36	44.85
7	1.10	34.74	34.42
11	1.35	26.36	28.75
15	1.59	28.17	29.79
19	1.77	37.46	31.48
23	1.95	33.34	37.72
27	2.09	35.46	35.16
31	2.27	28.95	31.74
35	2.45	22.78	25.74
39	2.62	21.83	22.12
43	2.74	24.87	25.53
47	2.88	34.17	31.19
51	3.06	24.65	28.60
55	3.22	21.03	30.28
59	3.38	20.75	28.55
63	3.49	25.50	28.18
67	3.63	33.14	31.37
71	3.77	24.96	34.09
75	3.89	23.97	30.27
79	3.98	29.13	26.82
83	4.31	25.37	25.38
87	4.56	21.66	27.27
91	5.05	22.02	27.64
95	5.20	28.78	23.72
99	5.33	26.02	21.21
103	5.29	27.79	22.09
107	5.26	29.86	28.90
110	5.25	26.24	24.79