

Surface Mount Dual Low Pass Filter B14-EDU2267/2

Typical Performance Data

FREQUENCY	INSERTION LOSS		RETURN LOSS	
(MHz)	(dB)		(dB)	
	LPF-1	LPF-2	LPF-1	LPF-2
1	0.03	0.03	49.83	50.94
10	0.05	0.05	48.86	48.83
50	0.09	0.08	42.61	40.90
100	0.12	0.12	39.17	35.88
200	0.19	0.18	33.76	28.95
250	0.22	0.21	31.60	26.50
500	0.37	0.37	22.00	19.47
600	0.45	0.45	19.29	17.64
750	0.59	0.59	16.33	15.79
900	0.76	0.75	14.35	14.76
1200	1.33	1.27	11.21	13.21
1330	1.89	1.92	9.65	10.78
1400	2.32	2.56	9.32	9.73
1500	3.43	4.54	10.54	9.43
1650	19.73	22.41	6.10	2.91
1700	30.46	32.72	3.21	2.00
2000	49.45	49.41	0.81	0.76
3500	48.37	49.44	0.50	0.43
4500	38.78	40.42	0.52	0.49
5200	35.71	38.39	0.56	0.51