

Typical Performance Data

FREQUENCY	INSERTION LOSS	RETURN LOSS
(MHz)	(dB)	(dB)
0.3	71.98	0.00
1.0	61.00	0.00
10.0	41.01	0.00
100.0	27.08	0.07
300.0	33.48	0.15
500.0	43.44	0.17
1000.0	38.91	0.21
1200.0	36.58	0.23
1400.0	36.45	0.25
1500.0	37.83	0.27
1550.0	39.28	0.29
1600.0	41.91	0.30
1650.0	47.03	0.32
1700.0	49.49	0.34
1750.0	39.95	0.36
1800.0	33.85	0.40
1850.0	29.24	0.45
1900.0	25.31	0.52
1950.0	21.73	0.62
2000.0	18.31	0.78
2200.0	5.68	4.45
2320.0	2.09	23.14
2340.0	1.92	41.39
2360.0	1.81	25.39
2380.0	1.73	20.48
2400.0	1.68	18.17
2420.0	1.64	16.99
2440.0	1.61	16.50
2460.0	1.58	16.49
2480.0	1.56	16.82
2500.0	1.55	17.33
2520.0	1.55	17.68
2530.0	1.55	17.65
2700.0	3.09	6.01
2800.0	5.27	2.99
3000.0	9.98	1.08
3200.0	13.93	0.60
3400.0	17.21	0.44
3580.0	19.86	0.38
3600.0	20.15	0.38
3800.0	22.91	0.36
4000.0	25.73	0.36
4200.0	28.94	0.35
4400.0	32.76	0.36
4600.0	38.08	0.36
5000.0	47.93	0.38
5200.0	39.56	0.39
5400.0	36.03	0.40
5600.0	34.22	0.41
6000.0	33.89	0.47