

Typical Performance Data

FREQUENCY	INSERTION LOSS	RETURN LOSS
(MHz)	(dB)	(dB)
0.3	65.58	0.01
0.7	58.50	0.01
1.0	55.45	0.00
3.0	45.97	0.00
7.0	38.68	0.00
10.0	35.71	0.00
30.0	27.65	0.02
70.0	25.45	0.08
100.0	26.43	0.11
300.0	37.88	0.18
700.0	38.27	0.25
1000.0	42.94	0.35
1100.0	33.77	0.47
1160.0	24.12	0.64
1180.0	21.37	0.75
1200.0	18.70	0.89
1300.0	6.24	4.57
1400.0	2.32	12.34
1410.0	2.28	12.12
1420.0	2.23	12.16
1430.0	2.19	12.46
1440.0	2.14	13.07
1450.0	2.10	14.02
1460.0	2.06	15.41
1470.0	2.03	17.38
1480.0	2.02	19.95
1490.0	2.04	22.13
1500.0	2.09	20.87
1550.0	3.00	8.49
1600.0	4.93	4.00
1700.0	9.49	1.37
1750.0	11.50	0.95
1800.0	13.28	0.73
1900.0	16.30	0.50
2000.0	18.79	0.40
2050.0	19.89	0.37
2200.0	22.84	0.31
2400.0	26.38	0.29
2500.0	28.13	0.28
2600.0	29.89	0.27
2700.0	31.68	0.27
2800.0	33.65	0.28
2900.0	35.88	0.28
3000.0	38.51	0.29
3200.0	47.33	0.30
3400.0	51.75	0.32
3500.0	45.15	0.33
3700.0	38.98	0.35
3800.0	37.12	0.37
4000.0	34.60	0.39