

Typical Performance Data

FREQUENCY	INSERTION LOSS	RETURN LOSS
(MHz)	(dB)	(dB)
0.3	67.54	0.02
0.7	60.16	0.00
1.0	56.83	0.00
3.0	47.30	0.00
7.0	40.01	0.00
10.0	36.95	0.00
30.0	28.08	0.02
70.0	23.46	0.06
100.0	23.01	0.09
300.0	29.56	0.18
700.0	43.29	0.24
1000.0	34.53	0.29
1100.0	34.50	0.32
1200.0	37.32	0.36
1300.0	49.47	0.43
1350.0	33.72	0.49
1500.0	14.77	1.16
1700.0	2.07	13.40
1750.0	1.90	11.93
1755.0	1.89	11.94
1800.0	1.74	13.62
1810.0	1.70	14.49
1854.0	1.60	23.61
1876.0	1.63	28.22
1898.0	1.73	18.28
1920.0	1.94	13.21
2018.0	4.00	4.48
2116.0	6.90	2.02
2214.0	9.64	1.15
2312.0	12.00	0.78
2410.0	14.03	0.59
2508.0	15.80	0.49
2704.0	18.82	0.39
2802.0	20.15	0.37
2900.0	21.40	0.35
3000.0	22.64	0.35
3100.0	23.87	0.34
3300.0	26.34	0.34
3500.0	28.81	0.36
3600.0	30.24	0.36
3800.0	33.47	0.39
3900.0	35.44	0.40
4000.0	37.80	0.41
4100.0	40.43	0.42
4300.0	45.71	0.44
4500.0	42.97	0.46
4700.0	40.18	0.47
4800.0	39.10	0.47
4900.0	38.29	0.49
5000.0	37.78	0.49