

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
100	92.13	0.00
500	78.54	0.01
1000	72.99	0.00
2000	67.82	0.02
3000	65.21	0.01
4000	65.11	0.00
5000	69.14	0.11
6000	68.70	0.02
7000	53.68	0.05
8000	45.03	0.23
8800	52.98	0.46
10000	2.55	10.34
10700	1.04	22.26
11600	0.95	22.45
12200	1.01	26.06
12700	1.21	18.86
13000	1.49	15.93
13200	1.73	20.28
13400	2.55	13.20
13600	5.27	5.01
13800	10.21	2.10
14000	15.89	1.11
14200	21.95	0.72
14400	28.31	0.58
14600	35.98	0.46
14800	47.57	0.44
15000	47.04	0.37
15100	44.00	0.33
15500	39.83	0.29
16000	39.35	0.27
16500	40.00	0.26
17000	40.93	0.20
17500	41.80	0.11
18000	42.53	0.06
18500	43.15	0.10
19000	43.81	0.16
19500	44.37	0.17
20000	44.75	0.16
20500	44.96	0.14
21000	45.14	0.16
21500	45.24	0.21
22000	45.29	0.22
22500	45.18	0.16
23000	45.04	0.07
23500	45.03	0.03
24000	45.05	0.03
24500	45.08	0.07
25000	45.07	0.07
25500	45.09	0.03
26000	44.99	0.01
26500	44.83	0.01
27000	44.39	0.03
28000	42.66	0.03
29000	38.58	0.00
30000	24.44	0.23
30500	35.20	0.48
31000	33.69	0.40
31500	37.64	0.84
32000	45.53	0.41
32500	46.04	0.22
33000	45.93	0.14
33500	44.75	0.11
34000	43.01	0.13
35000	38.92	0.27
36000	34.07	0.32
37000	28.39	0.12
38000	21.02	0.00
39000	8.54	1.32
40000	15.37	1.00