

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
100	97.10	0.07
500	84.48	0.14
1000	79.18	0.21
2000	73.57	0.19
3000	70.63	0.11
4000	68.41	0.06
5000	67.12	0.03
6000	66.55	0.01
7000	65.79	0.04
8000	66.30	0.01
9000	67.80	0.02
10000	71.16	0.05
11000	79.55	0.04
12000	75.89	0.05
13000	65.24	0.12
14000	59.29	0.26
13000	65.24	0.12
14000	59.29	0.26
15000	55.18	0.34
16000	52.45	0.27
17000	49.79	0.14
18000	46.72	0.12
19000	43.20	0.17
20000	39.64	0.26
21000	36.63	0.38
22000	33.84	0.47
22200	33.28	0.50
23000	32.61	0.61
24000	23.39	1.08
25000	2.66	13.77
26000	1.26	18.05
27000	1.05	31.01
27500	1.03	27.95
28000	1.03	23.58
28500	1.03	21.97
29000	1.03	22.96
29500	1.03	25.96
30000	1.07	25.18
31000	1.35	21.29
32000	2.69	27.64
33000	28.71	1.11
34000	30.68	0.17
35000	31.09	0.10
35300	31.23	0.17
36000	31.52	0.49
37000	33.34	0.90
38000	37.43	0.59
39000	41.94	0.14
40000	45.51	0.01
41000	48.52	0.18
42000	52.13	0.32
43000	57.09	0.25
44000	62.10	0.03
45000	63.65	-0.05
46000	60.96	0.14
47000	56.35	0.43
48000	54.31	0.53
49000	52.15	0.39
50000	50.80	0.15
51000	48.28	0.24
52000	45.92	0.78
53000	45.26	1.01
54000	45.29	0.59
55000	41.74	-0.08
56000	35.63	-0.36
57000	33.11	-0.10
58000	30.66	0.92
59000	28.86	2.21
60000	28.54	2.52