

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
10	53.79	0.01
500	82.01	0.29
1000	76.49	0.38
2000	72.06	0.33
4000	63.57	0.50
6000	60.71	0.88
8000	60.85	0.90
10000	56.27	1.26
12000	51.65	1.39
14000	49.14	1.29
16000	43.63	1.87
18000	41.98	1.52
20000	39.84	1.86
21700	53.55	2.26
22000	42.83	2.30
24000	2.32	12.94
24100	2.28	11.68
24200	2.21	11.39
24250	2.17	11.47
24300	2.12	11.80
24350	2.06	12.10
24400	2.00	12.53
24450	1.94	13.23
24500	1.86	13.94
24550	1.81	14.78
24560	1.79	14.97
25000	1.46	26.07
25200	1.43	21.47
25400	1.42	19.49
25600	1.44	18.64
25800	1.49	17.15
26000	1.64	14.78
26050	1.68	14.32
26100	1.74	13.64
26150	1.80	13.02
26200	1.85	12.67
26250	1.92	12.16
26300	1.98	11.66
26350	2.05	11.47
26400	2.11	11.08
26450	2.18	10.73
26500	2.23	10.68
26600	2.34	10.30
26700	2.42	10.43
26800	2.48	10.58
26900	2.52	10.88
27000	2.54	11.86
27100	2.55	12.82
27200	2.57	14.40
27300	2.66	16.25
27400	2.87	16.29
27500	3.24	14.47
28000	8.70	5.33
29000	26.16	3.12
29430	32.68	2.86
30000	38.18	2.42
31000	38.68	2.46
32000	44.43	2.67
33000	38.27	3.08
34000	38.11	2.86
35000	40.95	2.58
35400	43.16	2.51
36000	44.59	2.49
38000	32.82	2.99
40000	39.07	2.56
42000	37.50	2.67
44000	38.74	3.60
46000	49.95	2.87
48000	25.72	4.29
50000	10.66	4.74