

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
100	107.61	0.07
500	113.00	0.19
1000	108.59	0.23
2000	130.32	0.10
4000	112.99	0.06
6000	116.33	0.27
8000	109.93	0.04
10000	107.25	0.43
12000	111.28	0.19
14000	107.52	0.31
16000	103.84	-0.02
18000	104.12	0.34
20000	90.65	0.08
22000	77.23	0.11
24000	57.52	0.37
26000	24.39	0.78
28000	1.67	30.37
28500	1.43	25.82
29000	1.37	13.89
29500	1.46	11.27
30000	1.27	15.80
30500	1.23	23.95
31000	1.59	13.39
31500	1.87	11.60
32000	1.90	11.30
32500	1.72	11.52
33000	1.49	11.95
33500	1.47	11.39
34000	1.58	11.08
34500	1.69	12.21
35000	1.70	18.09
35500	1.78	26.90
36000	1.82	22.69
37000	2.26	14.88
38000	12.84	1.81
39000	33.25	0.41
40000	48.93	1.09
41000	61.83	1.16
42000	75.95	0.14
43000	87.21	0.19
44000	86.29	0.72
45000	87.23	0.32
46000	89.24	-0.02
47000	88.63	0.12
48000	82.72	-0.13
49000	87.56	-0.26
50000	89.19	-0.10
52000	88.27	-0.54
54000	94.30	-0.89
56000	90.10	0.24
58000	99.49	0.07
60000	99.96	-0.15
62000	76.92	0.85
64000	69.01	1.53
66000	59.53	1.11
67000	72.94	0.46