

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
100	113.36	0.13
200	115.77	0.17
400	106.96	0.24
600	106.90	0.28
800	105.49	0.31
1000	102.20	0.32
1200	100.00	0.33
1400	97.49	0.32
1600	97.67	0.31
1800	95.83	0.30
2000	93.89	0.30
2200	93.25	0.31
2400	91.83	0.32
2600	90.57	0.35
2800	90.11	0.39
3000	88.32	0.43
3200	86.58	0.47
3400	84.39	0.52
3500	83.07	0.54
4000	72.65	0.62
4500	53.91	0.66
5000	19.55	1.63
5200	3.15	23.97
5350	2.33	24.43
5400	2.27	19.03
5450	2.23	18.33
5500	2.16	20.73
5550	2.12	25.86
5600	2.09	30.91
5650	2.11	22.61
5700	2.16	18.18
5750	2.18	17.25
5800	2.19	17.76
5850	2.18	19.37
5900	2.16	24.48
5950	2.16	30.30
6000	2.19	26.61
6050	2.23	23.18
6100	2.28	21.35
6150	2.31	21.75
6200	2.35	24.58
6250	2.39	27.02
6300	2.46	23.78
6350	2.53	20.44
6400	2.65	17.42
6450	2.72	16.50
6500	2.82	16.47
6550	2.88	17.34
6600	2.95	20.23
6650	3.00	23.66
6700	3.11	30.02
7000	4.31	27.63
7500	37.75	2.13
8000	77.58	1.29
8500	80.78	1.12
9000	78.58	1.02
9500	77.42	1.06
10000	76.65	1.19
10500	76.29	1.31
11000	76.66	1.35
11500	77.76	1.22
12000	78.76	1.07
12500	79.87	1.08
13000	80.68	1.18
13500	81.70	1.40
14000	83.24	1.63
14500	86.22	1.67
15000	92.38	1.60
15500	103.42	1.53
16000	98.96	1.57
16500	68.98	1.96
17000	25.44	10.62