

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
10	96.63	0.08
50	93.25	0.09
100	102.19	0.12
500	105.73	0.26
1000	104.92	0.32
1500	101.28	0.31
2000	99.16	0.30
2500	94.74	0.33
3000	96.51	0.40
3500	98.11	0.50
4000	94.03	0.57
4500	94.30	0.55
5000	96.74	0.57
5500	88.80	0.62
6000	78.21	0.71
6500	69.22	0.82
7000	56.34	0.90
7500	38.17	1.09
7600	33.60	1.18
7700	28.57	1.31
7800	22.99	1.54
7900	16.77	2.03
8000	10.18	3.40
8100	4.79	8.13
8200	2.63	21.04
8300	2.14	33.51
8400	1.95	35.67
8500	1.86	30.20
8600	1.81	28.91
8700	1.78	33.66
8800	1.76	40.55
8900	1.76	30.42
9000	1.77	27.01
9100	1.79	26.30
9200	1.80	27.53
9300	1.81	30.93
9400	1.82	37.93
9500	1.84	49.11
9600	1.87	35.25
9700	1.90	30.21
9800	1.94	27.07
9900	1.98	25.81
10000	2.02	25.28
10100	2.06	26.83
10200	2.10	30.82
10300	2.15	47.59
10400	2.23	32.25
10500	2.32	26.51
10600	2.41	24.40
10700	2.51	24.51
10800	2.62	26.96
10900	2.75	33.59
11000	2.93	38.86
11500	5.53	18.94
12000	32.03	3.19
12500	58.10	1.81
13000	79.17	1.42
14000	94.48	1.36
15000	98.02	1.53
16000	99.54	1.65
17000	94.27	1.53
18000	114.20	1.45
19000	111.19	1.55
20000	105.76	1.67
21000	112.01	1.77
22000	90.60	1.93
23000	91.64	2.02
24000	78.71	1.93
25000	71.62	2.23
26000	47.93	4.98
27000	10.55	10.26