

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1.0	0.21	24.91	1.0	48.070
3.0	0.26	20.32	1.1	47.910
5.0	0.30	20.46	1.3	48.210
7.0	0.33	25.27	1.4	47.670
9.0	0.38	24.09	1.6	48.070
11.0	0.47	20.00	1.8	47.680
13.0	0.58	19.00	2.0	48.300
15.0	0.81	16.36	2.3	48.440
17.0	2.32	7.61	2.5	48.370
19.0	8.82	2.63	2.9	48.630
19.8	12.25	2.04	3.2	48.630
20.6	15.66	1.72	3.6	48.800
21.4	18.93	1.51	4.0	48.880
22.2	22.02	1.36	4.6	49.480
23.0	24.94	1.25	5.1	49.490
23.8	27.72	1.15	5.8	50.430
25.4	32.87	0.99	6.5	50.770
27.1	37.90	0.86	7.3	51.870
28.7	42.24	0.76	8.2	53.050
30.4	46.55	0.67	9.3	54.470
32.0	50.45	0.60	10.4	56.610
33.6	54.18	0.55	11.7	60.330
54.4	77.82	0.22	13.1	66.080
75.2	77.17	0.12	15.0	80.270
96.0	81.80	0.09	17.0	100.530
116.8	80.95	0.08	18.8	81.420
137.6	80.75	0.07	21.1	43.840
158.4	83.26	0.07	23.0	28.310
179.2	79.58	0.06	26.6	15.720
200.0	80.96	0.06	30.0	10.370