

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1.00	81.96	0.01	1.00	48.04
5.00	67.64	0.01	5.00	0.18
10.00	61.63	0.01	10.00	2.60
20.00	55.79	0.02	20.00	2.08
40.00	50.76	0.04	50.00	2.63
50.00	49.91	0.06	80.00	6.97
90.00	48.42	0.30	90.00	4.23
94.00	36.78	0.41	94.00	8.69
96.00	31.69	0.49	100.00	16.22
98.00	26.84	0.61	105.00	30.34
100.00	22.11	0.78	110.00	42.71
105.00	10.79	2.02	115.00	29.71
110.00	3.06	8.86	120.00	22.32
115.00	1.38	23.64	130.00	16.93
130.00	0.95	18.66	140.00	15.35
140.00	0.88	24.14	150.00	15.63
150.00	0.94	29.69	160.00	18.00
165.00	1.41	16.88	165.00	21.42
170.00	2.26	10.78	170.00	28.25
180.00	12.41	1.43	175.00	27.32
186.00	20.61	0.81	180.00	17.43
190.00	25.91	0.66	184.00	11.90
195.00	32.48	0.55	190.00	7.72
200.00	39.28	0.49	200.00	4.10
250.00	58.22	0.32	250.00	0.94
300.00	49.20	0.31	300.00	0.41
400.00	46.28	0.33	400.00	0.54
500.00	43.65	0.36	500.00	0.41
800.00	30.89	0.70	800.00	1.20
1000.00	62.43	0.57	1000.00	2.07