

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1.00	89.09	0.01	1.00	16.28
5.00	75.19	0.01	5.00	0.52
10.00	69.05	0.02	10.00	1.75
20.00	63.78	0.03	20.00	0.84
50.00	62.86	0.07	50.00	2.39
80.00	47.69	0.18	70.00	26.17
90.00	28.27	0.39	90.00	10.13
95.00	19.08	0.71	95.00	15.83
100.00	9.99	1.94	100.00	27.15
105.00	3.48	7.73	105.00	37.20
110.00	1.65	24.42	110.00	28.25
120.00	1.11	25.57	120.00	18.42
130.00	0.95	27.97	130.00	15.25
140.00	0.93	25.29	140.00	13.94
150.00	0.99	21.99	150.00	13.79
160.00	1.07	26.90	160.00	14.92
170.00	1.35	32.39	170.00	18.78
175.00	2.07	12.75	175.00	22.76
200.00	23.43	0.77	180.00	23.12
204.00	26.98	0.68	185.00	17.32
210.00	31.99	0.59	190.00	12.02
220.00	39.90	0.49	200.00	6.49
230.00	47.69	0.44	220.00	3.09
300.00	69.59	0.34	250.00	4.02
400.00	59.00	0.35	300.00	10.14
500.00	56.95	0.38	400.00	3.29
600.00	54.71	0.40	500.00	0.37
800.00	34.70	0.55	600.00	2.11
900.00	33.47	0.95	800.00	1.79
1000.00	49.66	0.70	1000.00	2.07