

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
0.50	109.40	0.00	0.50	83.88
1.00	101.20	0.00	1.00	83.81
5.00	93.86	0.00	5.00	82.03
10.00	87.96	0.01	10.00	62.50
50.00	91.27	0.01	60.00	3.69
100.00	93.03	0.04	100.00	3.08
110.00	89.64	0.07	110.00	4433.91
120.00	63.06	0.11	120.00	54.19
129.50	46.83	0.23	140.00	11.79
133.00	40.39	0.30	146.00	36.93
135.00	36.46	0.37	151.00	50.87
139.50	26.85	0.65	154.00	37.80
142.00	20.79	1.00	159.00	36.27
145.00	12.79	2.13	164.00	34.30
149.00	4.22	10.90	167.00	36.58
151.00	2.82	20.52	169.00	33.50
154.00	2.21	29.80	172.00	23.17
159.00	1.88	22.07	177.00	11.72
162.00	1.83	24.00	180.00	8.58
167.00	1.89	40.48	185.00	6.05
170.00	2.23	20.14	188.00	5.49
180.00	12.01	1.45	200.00	64.81
186.00	19.15	0.61	210.00	9.91
193.00	25.50	0.35	230.00	6.84
200.00	30.25	0.23	250.00	1.02
208.00	34.40	0.17	500.00	0.45
222.00	39.66	0.11	1000.00	0.80
250.00	46.03	0.08	1400.00	0.35
1000.00	63.28	0.27	1600.00	0.31
1700.00	17.79	1.25	1700.00	0.31