

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
0.50	67.85	0.40	150.00	21.91
1.00	68.01	0.41	155.00	39.19
5.00	71.26	0.46	160.00	41.65
10.00	73.06	0.46	160.50	40.49
60.00	70.84	0.26	161.00	39.61
100.00	68.97	0.16	161.50	38.77
113.00	60.57	0.16	162.00	37.83
126.00	46.32	0.19	162.50	36.91
130.00	41.72	0.21	164.00	34.65
135.00	35.39	0.27	166.00	31.96
141.00	26.21	0.51	168.00	30.19
145.00	18.98	0.98	170.00	29.88
150.00	8.78	3.74	172.00	30.01
162.00	2.23	12.73	173.00	29.66
166.00	2.21	11.76	174.00	29.96
172.00	2.08	21.20	176.00	30.51
174.00	2.11	21.97	178.00	31.02
182.00	3.16	13.65	180.00	33.11
189.00	10.58	2.73	182.00	37.17
186.00	6.43	6.29	182.50	38.60
195.00	19.30	1.08	183.00	39.81
200.00	25.10	0.74	183.50	40.61
205.00	29.93	0.57	184.00	41.36
220.00	40.63	0.36	184.50	41.76
230.00	45.95	0.28	185.00	42.30
500.00	75.68	0.06	186.00	40.76
1000.00	64.21	0.18	187.00	37.83
2000.00	56.62	0.40	188.00	33.65
5000.00	14.70	10.14	189.00	29.95
6000.00	27.70	1.94	190.00	24.92