

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
0.50	74.39	0.43	0.50	13.76
1.00	74.17	0.43	1.00	13.37
10.00	71.31	0.47	10.00	9.10
50.00	68.30	0.27	50.00	1.15
100.00	59.17	0.15	100.00	7.92
110.00	45.47	0.24	110.00	3.29
112.00	42.48	0.23	112.00	6.73
121.00	25.71	0.71	121.00	16.53
122.00	23.47	0.83	122.00	19.19
130.00	4.71	10.02	130.00	64.32
132.00	3.18	21.27	132.00	57.78
133.00	2.93	25.52	133.00	53.72
135.00	2.57	25.31	135.00	47.39
140.00	2.36	20.28	140.00	41.78
145.00	2.61	22.19	145.00	43.91
147.00	2.86	22.65	147.00	48.85
150.00	4.65	9.60	150.00	56.12
158.00	20.06	1.22	158.00	15.84
162.00	26.49	0.82	162.00	10.25
164.00	29.10	0.68	164.00	7.69
173.00	39.10	0.41	173.00	3.19
178.00	42.85	0.35	178.00	2.73
180.00	44.75	0.32	180.00	8.15
500.00	77.89	0.17	500.00	0.13
1000.00	63.63	0.38	1000.00	0.37
2000.00	58.80	0.04	2000.00	0.70
5000.00	36.31	1.46	5000.00	0.78
6000.00	20.31	1.84	6000.00	0.76
8000.00	33.34	2.53	8000.00	0.39
8500.00	28.36	3.75	8500.00	2.64