

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
0.5	101.19	0.00	400.0	14.41
10.0	66.66	0.02	405.0	12.24
50.0	52.46	0.00	410.0	10.69
100.0	48.52	0.01	415.0	9.48
300.0	47.96	0.24	420.0	8.52
365.0	38.02	1.37	440.0	6.15
380.0	23.12	6.44	460.0	5.09
385.0	15.78	8.31	480.0	4.54
390.0	9.93	9.44	500.0	4.18
395.0	6.29	11.15	520.0	3.92
400.0	4.08	13.68	540.0	3.71
405.0	2.79	16.22	560.0	3.58
415.0	1.60	16.01	570.0	3.55
420.0	1.34	14.68	600.0	3.55
480.0	0.79	17.19	620.0	3.67
520.0	0.65	23.35	640.0	3.88
570.0	0.81	16.61	660.0	4.13
620.0	0.82	21.65	680.0	4.55
680.0	0.92	29.02	700.0	5.18
720.0	1.44	19.49	720.0	6.32
740.0	2.58	13.95	725.0	6.78
750.0	4.60	9.02	730.0	7.29
760.0	8.04	4.99	735.0	7.91
775.0	15.29	2.23	740.0	8.56
800.0	29.71	1.12	750.0	9.69
830.0	50.28	0.80	760.0	9.84
835.0	54.21	0.78	770.0	8.75
900.0	54.32	0.71	780.0	7.01
1000.0	52.25	0.69	790.0	5.45
1600.0	50.24	0.50	800.0	4.19