

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.0	62.99	0.01	550.0	23.66
100.0	44.57	0.01	554.0	18.53
200.0	44.52	0.03	560.0	14.31
220.0	46.15	0.04	570.0	10.82
320.0	47.67	0.10	580.0	8.70
526.0	32.88	0.79	590.0	7.61
530.0	23.61	0.97	600.0	7.06
534.0	15.24	1.30	610.0	6.73
538.0	9.07	2.15	620.0	6.42
542.0	5.34	4.79	624.0	6.30
546.0	3.54	10.09	630.0	6.21
560.0	1.84	14.10	640.0	6.16
590.0	1.44	11.22	650.0	6.41
625.0	1.18	12.53	660.0	6.89
660.0	1.36	14.48	670.0	7.52
690.0	1.87	20.54	680.0	8.46
704.0	2.82	20.18	690.0	9.95
710.0	4.25	9.63	698.0	12.11
716.0	6.92	4.90	704.0	14.73
722.0	10.64	2.94	710.0	16.86
728.0	15.25	2.09	716.0	15.43
734.0	20.60	1.67	722.0	11.47
752.0	38.95	1.16	728.0	7.95
900.0	46.55	0.63	734.0	5.51
920.0	50.72	0.64	740.0	3.69
1000.0	53.77	0.63	750.0	1.92