

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1	88.30	0.00	400	13.12
50	55.08	0.01	410	12.73
100	48.62	0.02	414	11.89
340	37.64	0.31	420	10.54
380	16.37	0.86	424	9.85
390	8.98	1.72	428	9.34
395	5.88	2.85	430	9.15
400	3.59	5.03	432	9.00
410	1.66	13.26	434	8.88
420	1.30	18.86	436	8.77
430	1.19	25.91	438	8.68
440	1.17	25.16	440	8.61
450	1.25	17.55	442	8.56
460	1.37	15.54	444	8.54
470	1.51	17.65	446	8.51
485	2.69	12.98	448	8.51
490	4.17	7.76	450	8.53
500	9.36	3.05	454	8.62
510	15.71	1.61	458	8.81
530	28.18	0.81	460	8.95
540	34.44	0.65	466	9.57
600	57.63	0.27	470	10.17
1000	52.99	0.18	480	11.97
1500	51.56	0.27	500	10.40