

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
0.03	78.67	0.01	110.00	19.66
10.00	68.58	0.00	115.00	17.79
50.00	54.01	0.01	118.00	38.26
110.00	52.44	0.28	120.00	56.62
115.00	30.24	0.62	123.00	65.75
116.00	26.06	0.78	125.00	57.19
118.00	17.71	1.39	128.00	42.02
120.00	9.78	3.42	130.00	36.95
122.00	4.61	12.24	132.00	33.59
124.00	2.83	17.85	136.00	30.14
125.00	2.47	15.69	138.00	29.23
130.00	1.79	18.17	140.00	28.59
134.00	1.55	20.10	142.00	28.31
140.00	1.50	18.55	144.00	28.66
144.00	1.65	14.34	146.00	29.82
150.00	1.82	20.25	148.00	31.74
155.00	2.74	25.13	150.00	34.35
158.00	5.79	8.19	152.00	38.29
160.00	10.68	3.30	154.00	44.72
163.00	19.32	1.32	158.00	51.95
167.00	30.31	0.68	160.00	44.52
174.00	50.10	0.35	163.00	26.20
200.00	57.05	0.13	165.00	17.67
400.00	49.20	0.05	170.00	7.37