

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1.0	88.28	0.05	350	4.29
10.0	67.47	0.04	400	2.83
200.0	75.46	0.17	450	2.19
240.0	31.42	0.34	500	1.86
255.0	20.21	0.52	550	1.66
350.0	0.66	17.68	600	1.52
455.0	0.62	14.70	650	1.41
485.0	0.60	15.18	700	1.32
550.0	0.56	17.31	750	1.26
560.0	0.56	17.55	800	1.22
650.0	0.62	15.67	850	1.21
1010.0	0.64	23.44	900	1.21
1670.0	1.88	15.41	950	1.22
1690.0	2.55	9.83	1000	1.23
1700.0	3.14	7.64	1010	1.23
1820.0	19.59	0.95	1100	1.24
1890.0	29.99	0.71	1200	1.28
2170.0	49.35	0.47	1200	1.28
2250.0	53.86	0.40	1300	1.38
2700.0	47.78	0.36	1350	1.43
3190.0	53.70	1.80	1400	1.49
3490.0	52.24	2.36	1500	1.70
3760.0	55.45	1.22	1600	2.17
4000.0	67.83	0.65	1670	3.10