

Surface Mount Band Pass Filter

BPF-EDU2115

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1	106.17	0.05	950	4.36
90	106.74	0.04	960	4.07
480	54.03	0.13	990	3.18
585	72.72	0.20	1025	2.56
725	44.43	0.44	1075	2.15
785	48.15	1.22	1100	2.03
825	33.33	1.54	1150	1.87
845	22.10	1.18	1200	1.79
900	5.36	3.26	1230	1.78
950	1.14	21.87	1270	1.80
1000	1.01	15.93	1300	1.84
1105	0.84	19.05	1310	1.87
1200	0.85	18.01	1330	1.92
1350	0.91	19.90	1350	1.99
1450	1.24	18.91	1360	2.04
1520	3.16	9.94	1370	2.09
1570	17.76	1.56	1390	2.21
1595	30.21	1.12	1395	2.25
1620	46.03	0.96	1400	2.29
1665	41.75	0.82	1410	2.38
1725	50.90	0.73	1420	2.49
1915	38.50	0.66	1430	2.62
2000	43.17	0.66	1440	2.78
2560	29.14	0.63	1450	2.99