

# Fixed Attenuator

# BW-S1-2W263A+

## Typical Performance Data

| FREQUENCY<br>(GHz) | ATTENUATION<br>(dB) | VSWR<br>(:1) |
|--------------------|---------------------|--------------|
| 0.01               | 0.83                | 1.01         |
| 0.2                | 0.84                | 1.01         |
| 0.3                | 0.84                | 1.01         |
| 0.4                | 0.85                | 1.01         |
| 0.5                | 0.85                | 1.01         |
| 0.6                | 0.85                | 1.01         |
| 0.7                | 0.85                | 1.01         |
| 0.8                | 0.86                | 1.01         |
| 0.9                | 0.86                | 1.01         |
| 1.0                | 0.86                | 1.01         |
| 2.0                | 0.87                | 1.02         |
| 3.0                | 0.89                | 1.02         |
| 4.0                | 0.90                | 1.03         |
| 5.0                | 0.91                | 1.04         |
| 6.0                | 0.93                | 1.05         |
| 7.0                | 0.94                | 1.07         |
| 8.0                | 0.96                | 1.08         |
| 9.0                | 0.98                | 1.09         |
| 10.0               | 1.00                | 1.09         |
| 11.0               | 1.02                | 1.09         |
| 12.0               | 1.04                | 1.10         |
| 13.0               | 1.06                | 1.09         |
| 14.0               | 1.09                | 1.10         |
| 15.0               | 1.12                | 1.11         |
| 16.0               | 1.15                | 1.11         |
| 17.0               | 1.18                | 1.13         |
| 18.0               | 1.22                | 1.15         |
| 19.0               | 1.26                | 1.16         |
| 20.0               | 1.30                | 1.18         |
| 21.0               | 1.34                | 1.18         |
| 22.0               | 1.38                | 1.18         |
| 23.0               | 1.42                | 1.17         |
| 24.0               | 1.44                | 1.18         |
| 25.0               | 1.45                | 1.20         |
| 26.0               | 1.34                | 1.28         |

