

Test Cable, SMA-Male/SMA-Male

CBL-1.5M-SMSM+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
0.3	0.00	52.28	53.42
0.7	0.01	55.05	55.72
1.0	0.02	53.52	53.79
3.0	0.03	48.25	48.57
5.0	0.04	46.32	46.54
7.0	0.05	45.20	45.26
9.0	0.05	44.41	44.36
10.0	0.05	43.94	43.93
30.0	0.09	40.70	40.21
50.0	0.12	41.93	42.01
70.0	0.15	50.17	49.18
90.0	0.17	44.30	45.22
100.0	0.18	41.09	41.60
200.0	0.25	39.32	38.47
300.0	0.32	47.56	56.45
400.0	0.37	35.46	35.28
500.0	0.42	36.62	36.74
600.0	0.46	38.84	38.53
700.0	0.50	32.53	32.80
800.0	0.53	45.45	48.18
900.0	0.57	32.18	31.57
1000.0	0.60	35.26	36.08
1500.0	0.75	34.73	33.74
2000.0	0.87	35.97	34.34
2500.0	0.99	37.52	33.80
3000.0	1.09	50.10	34.61
3500.0	1.20	42.52	35.80
4000.0	1.28	41.26	35.46
4500.0	1.37	37.94	33.38
5000.0	1.47	38.51	38.01
5500.0	1.56	45.02	46.00
6000.0	1.63	42.48	38.76
6500.0	1.71	37.98	35.28
7000.0	1.78	36.39	32.54
7500.0	1.87	41.37	34.57
8000.0	1.93	44.24	57.62
8500.0	2.01	31.65	30.39
9000.0	2.08	30.28	30.42
9500.0	2.16	29.08	28.77
10000.0	2.23	30.77	31.52
11000.0	2.37	29.15	27.28
11500.0	2.42	39.14	29.50
12000.0	2.48	29.23	25.66
13000.0	2.64	24.35	24.65
14000.0	2.69	29.41	28.47
15000.0	2.81	29.72	25.32
16000.0	2.94	37.86	24.03
17000.0	3.03	31.48	25.29
18000.0	3.14	28.64	26.14