

Phase-Stable Flexible Cable SMA Male to SMA Male

CBN-15FT-SMSM+

Typical Performance Data

FREQ.	INSERTION LOSS	SMA MALE RETURN LOSS IN	SMA MALE RETURN LOSS OUT
(GHz)	(dB)	(dB)	(dB)
0	0.16	29.52	29.59
1	1.17	38.79	39.48
2	2.11	38.41	37.42
3	2.78	42.32	39.77
4	3.34	36.91	34.94
5	3.82	32.11	32.67
6	4.26	34.14	34.45
7	4.66	32.99	31.87
8	5.03	33.08	32.80
9	5.38	33.22	32.59
10	5.72	31.42	31.50
11	6.04	30.43	32.90
12	6.34	29.61	32.01
13	6.64	31.59	30.17
14	6.93	30.31	28.32
15	7.21	29.39	28.00
16	7.48	29.49	27.43
17	7.74	29.66	27.62
18	8.00	31.55	28.76
19	8.24	32.48	31.12
20	8.49	33.47	32.14
21	8.73	35.84	35.43
22	8.97	39.82	35.53
23	9.20	36.67	34.98
24	9.43	32.89	32.67
25	9.65	29.95	29.12
26	9.89	27.66	26.62
27	10.10	25.47	24.28