

Phase-Stable Flexible Cable TNC-Male to TNC-Male
CBN-1FT-TMTM+

Typical Performance Data			
FREQ.	INSERTION LOSS	TNC-MALE RETURN LOSS IN	TNC-MALE RETURN LOSS OUT
(GHz)	(dB)	(dB)	(dB)
0	0.03	48.53	47.94
1	0.14	38.06	38.78
2	0.19	37.53	36.79
3	0.23	31.94	30.87
4	0.26	33.84	31.98
5	0.29	35.19	30.65
6	0.31	38.85	30.13
7	0.34	27.39	29.22
8	0.36	28.77	33.10
9	0.41	25.66	24.97
10	0.43	29.53	27.96
11	0.48	23.60	24.27
12	0.51	24.13	24.33
13	0.50	30.63	31.38
14	0.52	28.36	29.83
15	0.53	37.73	35.40
16	0.57	24.86	25.57
17	0.60	26.68	27.12
18	0.61	28.92	26.88